Phone: +49 (0)731/1420-13 Fax: +49 (0)731/1420-82 e-mail: info@liqui-moly.de

Service-hotline: 0800/8323230 Technical hotline: +49 (0)731/1420-871 www.liqui-moly.de

Product information Pro-Line Rapid Rust Solvent

Description

Extremely fast-acting rust solvent with outstanding creep effect. Rapidly frees seized bolts and nuts. Penetrates even the narrowest of openings. Rust is infiltrated and loosened by the capillary action. Otherwise permanently seized screws and bolts are freed again in an instant. Dissolves dirt and protects against corrosion by displacing water. Rapid penetration and outstanding creep effect ensure low friction between the components to be freed.

Properties

- dissolves rust
- penetrtes fast
- does not attack plastics, rubber and paints
- excellent penetration action
- good corrosion protection
- infiltrates and drives out moisture
- extremely low friction
- also suitable for overhead work
- clean application

Technical data

Base	Ölkombination, Wirkstoffe / combination of oils, agents
Color / appearance	farblos / colourless
Density at 20 °C	0,829-0,86 g/ml DIN 51757
Operating temperature range	-40 bis +140 °C
Spreading rate (cover)	Stahlblech, blank / sheet steel, bright
	140-180 m²/l
Form	aerosol
Odor	charakteristisch / characteristic

Areas of application

The outstanding properties open up a wide range of applications in factories and workshops, on vehicles and on all household and hobby appliances. **Automotive applications:** Precise spot application allows the targeted treatment of screw connections and seals around bearings. Infiltrates, undermines and frees screw connections in all vehicle parts that have been attacked by corrosion. Industrial applications: For freeing all seized screw connections and bearings. Can be used as a release agent and preservative for metal plates. If the capillary tube is left folded in, corrosion protection can be applied to large areas. Can be used to facilitate assembly of bearings and slideways.

Application

Shake well before use. Depending on application, spray on in the desired quantity. A fold-out capillary tube ensures precision spraying. If the capillary tube is left folded in, large areas can be sprayed. Spray large areas without the capillary tube from about 20-25 cm. Overhead spraying also possible.

Available pack sizes

400 ml Can aerosol	7390 D-GB-I-E-P
400 ml Can aerosol	9917 GB-DK-FIN-N-S
400 ml Can aerosol	20678 D-NL-F-GR-RUS

Our information is based on thorough research and may be considered reliable, although not legally binding.



